

Model: JD-170 / JD-170G



- Emergency Call Button
- The Wrist Watch Transmitter is 100% waterproof
- Automatic fall detection (Model:JD-170G)
- Easy-to-carry to be wrist type
- Low battery and multiple call repeat alerts
- Durable battery life (20 times per day 6 month)
- Max alpha character: 64
- Max numeral character: 10
- The coverage can reach up to 200-300 M in open space, while it's about 100-200 meters indoor
- The Patient Call Watch JD-170 is waterproof and suitable for wearing even in a shower or for use in other wet environments such as hospitals, bathroom etc.


Frequency	430~450 450~470 865~875
RF Code Format	POCSAG
Transmitting Power	10 mW
Battery Type	CR2450 3V/600mA
Battery Life	20 times per day 6 month
Power Consumption	Sleep mode:<80uA TX mode : <60mA
Dimension (mm)	47(W)×41(H)×15(D)
Weight (with battery)	37 g

G sensor Level (Model:JD-170G)	
Level_5	1.5G
Level_4	1.75G
Level_3	2G
Level_2	2.25G
Level_1	2.5G

RECEIVER (OPTION)

ALPHANUMERIC PAGER

- » View Area: 45 x 14.43 mm
- » With 4-line display
- » 84 Alphanumeric




NURSE CALL STATION

- » Calling indicator with 50 LED lamps
- » Relay JD-170G signal to alphanumeric pager carried by nurse



DATA RADIO MODEM

- » POCSAG receiver
- » 2 relay outputs
- » Ethernet/Internet
- » Extending coverage with max. 32 units



ALPHA PAGER

NUMERIC PAGER

STONE PAGER

LED SIGN

VOICE PAGER

TRANSMITTER

TELEMETRY CONTROL

IN-HOUSE